

HIGH RESOLUTION 3D MICRO OR NANO COMPUTED TOMOGRAPHY & DIGITAL RADIOSCOPY SYSTEM

EasyTom XL



- High resolution 3D μComputed Tomography
- ▶ Real time high resolution 2D digital radioscopy
- ▶ Micro or nano and combined versions available
- Voxel resolution down to 350 nm/voxel
- Great versatility for a wide variety of applications and analyzable products
- ► Large inspection volume (diameter x height : 320 mm x 720 mm)
- ▶ Possible in situ µCT
- ▶ Programmable automatic control cycles
- Lead / Steel construction and X-ray safety interlocks, designed to meet X-ray safety regulations
- Open and comprehensive system, with programmable automatic control cycles

Technical Specifications

Safety Cabinet

- Footprint: 2750 x 1850 x 2400 mm
- Lead / Steel construction and X-ray safety interlocks, designed to meet X-ray safety regulations.
- Motorized door with automatic locker during X-Ray emission.
- Large scanning volume (diameter x height): 320 mm x 720 mm

Mechanics

- High accuracy motorized rotation and translation axis.
- Imager lateral and vertical shift option for enlarged field of view and decreased ring artifacts.
- Air-bearing rotation stage option, takes up of sample weight.

X-Ray generator

Several options and combinations available:

- Sealed or open type micro-focus tube (130 kV, 150kV)
- Open nano-focus tube (160 kV)
- Voltage up to 230 kV (several options available).
- Resolution down to 400nm/voxel
- Various targets and filament types available.

Imager

Several options and combinations available:

- High resolution flat panel detector
- Large area flat panel detector
- CCD sensor

Computers

- Various powerful GPU(s) configurations available.
- PC, High resolution display screen, Windows 10.

Softwares

RX Solutions X-Act software:

- Independent plugins to drive generator(s), imager(s), axes...
- Other plugins available for : dimensional measurements, video sequence acquisition, image filtering and processing, image export...
- CT acquisition:
 - advanced plugin with options (360° rotation, helical, continuous rotation, laminography...)
- Learning/Macros mode from automated workflow.
- CT reconstruction: GPU implementation including various filters

Post-processing software: 3D vizualisation, metrology, CAD comparison, defect analysis: in option







